

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844394

Luminaire Tested: **LD6C35DE010B35 EU6C35B35 6LBMH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P844394
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C35DE010B35 EU6C35B35 6LBMH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3213.1 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 41.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844394

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P844394

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	174323
5°	171197
10°	162450
15°	152339
20°	141873
25°	130725
30°	108922
35°	76767
40°	48927
45°	29174
50°	17219
55°	10953
60°	7554
65°	5344
70°	3687
75°	2902
80°	1421
85°	0



TEST NUMBER: P844394

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.7	9.0
10°-20°	752.1	23.4
20°-30°	974.6	30.3
30°-40°	723.5	22.5
40°-50°	305.5	9.5
50°-60°	108.5	3.4
60°-70°	41.9	1.3
70°-80°	14.5	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2017.5	62.8
0°-40°	2741.0	85.3
0°-60°	3154.9	98.2
0°-90°	3213.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3213.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3180	
5°	3111	291
15°	2684	752
25°	2161	975
35°	1147	724
45°	376	305
55°	115	108
65°	41	42
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P844394

CATALOG NUMBER: LD6C35DE010B35 EU6C35B35 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3179.9
2.5°	3170.6
5°	3111.0
7.5°	3023.8
10°	2918.3
12.5°	2803.5
15°	2684.2
17.5°	2551.2
20°	2431.9
22.5°	2308.0
25°	2161.2
27.5°	1959.2
30°	1720.7
32.5°	1440.7
35°	1147.1
37.5°	899.4
40°	683.7
42.5°	509.3
45°	376.3
47.5°	275.3
50°	201.9
52.5°	151.5
55°	114.6
57.5°	87.1
60°	68.9
62.5°	50.6
65°	41.2
67.5°	32.0
70°	23.0
72.5°	18.3
75°	13.7
77.5°	9.2
80°	4.5
82.5°	4.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)