

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P844481

Luminaire Tested: **LD6C40DE010B35 EU6C40B35 6LBMMW**

Issue Date: 5/7/2024



Test Information

Test Method: LM-79-08
Report Number: P844481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203577)
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C40DE010B35 EU6C40B35 6LBMMW
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3381.3 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844481

CATALOG NUMBER: LD6C40DE010B35 EU6C40B35 6LBMMW

Luminous Intensity Polar Plot





TEST NUMBER: P844481

CATALOG NUMBER: LD6C40DE010B35 EU6C40B35 6LBMMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138311
5°	136528
10°	131878
15°	126249
20°	119985
25°	111702
30°	96230
35°	73033
40°	53400
45°	40500
50°	33014
55°	28969
60°	26588
65°	24205
70°	21670
75°	19762
80°	17711
85°	14655



TEST NUMBER: P844481

CATALOG NUMBER: LD6C40DE010B35 EU6C40B35 6LBMWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.1	6.9
10°-20°	624.3	18.5
20°-30°	838.2	24.8
30°-40°	687.6	20.3
40°-50°	412.9	12.2
50°-60°	274.4	8.1
60°-70°	183.9	5.4
70°-80°	99.0	2.9
80°-90°	27.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1695.5	50.1
0°-40°	2383.1	70.5
0°-60°	3070.5	90.8
0°-90°	3381.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3381.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2523	
5°	2481	233
15°	2224	624
25°	1847	838
35°	1091	688
45°	522	413
55°	303	274
65°	187	184
75°	93	99
85°	23	28
90°	0	



TEST NUMBER: P844481

CATALOG NUMBER: LD6C40DE010B35 EU6C40B35 6LBMWW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2523.0
2.5°	2504.3
5°	2481.0
7.5°	2429.7
10°	2369.1
12.5°	2294.4
15°	2224.5
17.5°	2140.5
20°	2056.7
22.5°	1963.4
25°	1846.7
27.5°	1706.8
30°	1520.2
32.5°	1310.4
35°	1091.3
37.5°	904.7
40°	746.2
42.5°	620.3
45°	522.4
47.5°	443.0
50°	387.1
52.5°	340.5
55°	303.1
57.5°	270.5
60°	242.5
62.5°	209.8
65°	186.6
67.5°	158.5
70°	135.2
72.5°	111.9
75°	93.3
77.5°	74.6
80°	56.1
82.5°	42.0
85°	23.3
87.5°	9.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)