

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247004

Luminaire Tested: **LSR8B100D010 EC8B100830 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100830 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9956.9 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247004

CATALOG NUMBER: LSR8B100D010 EC8B100830 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247004

CATALOG NUMBER: LSR8B100D010 EC8B100830 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84	89	86	83	87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72	78	74	72	77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69	75	71	68	74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65	72	68	65	71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63	69	65	62	69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	779995
5°	738494
10°	556177
15°	386582
20°	288178
25°	216910
30°	145044
35°	75921
40°	29325
45°	10846
50°	2758
55°	538
60°	74
65°	270
70°	334
75°	0
80°	0
85°	425



TEST NUMBER: P247004

CATALOG NUMBER: LSR8B100D010 EC8B100830 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2074.5	20.8
10°-20°	3430.8	34.5
20°-30°	2892.3	29.0
30°-40°	1312.4	13.2
40°-50°	229.1	2.3
50°-60°	12.4	0.1
60°-70°	1.8	0.0
70°-80°	2.1	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8397.6	84.3
0°-40°	9710.1	97.5
0°-60°	9951.6	99.9
0°-90°	9956.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9956.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25295	
5°	23858	###
15°	12109	3431
25°	6375	2892
35°	2017	1312
45°	249	229
55°	10	12
65°	4	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247004

CATALOG NUMBER: LSR8B100D010 EC8B100830 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	25294.7
2.5°	25071.0
5°	23857.7
7.5°	21214.9
10°	17762.4
12.5°	14571.0
15°	12109.4
17.5°	10260.1
20°	8781.8
22.5°	7481.1
25°	6375.2
27.5°	5250.6
30°	4073.5
32.5°	2965.2
35°	2016.8
37.5°	1238.3
40°	728.5
42.5°	427.3
45°	248.7
47.5°	148.7
50°	57.5
52.5°	8.7
55°	10.0
57.5°	8.7
60°	1.2
62.5°	1.2
65°	3.7
67.5°	0.0
70°	3.7
72.5°	6.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.2
87.5°	3.7
90°	0.0

(END OF REPORT)