

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246960

Luminaire Tested: **LSR8B100D010 EC8B100835 8LBM0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100835 8LBMOLI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11178.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246960

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P246960

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	565646
5°	542062
10°	477978
15°	402815
20°	330739
25°	268066
30°	198454
35°	119456
40°	53200
45°	20684
50°	7417
55°	2167
60°	1523
65°	1138
70°	117
75°	620
80°	0
85°	1840



TEST NUMBER: P246960

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1598.7	14.3
10°-20°	3504.7	31.4
20°-30°	3574.2	32.0
30°-40°	2001.8	17.9
40°-50°	426.9	3.8
50°-60°	52.9	0.5
60°-70°	13.8	0.1
70°-80°	3.3	0.0
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8677.6	77.6
0°-40°	10679.4	95.5
0°-60°	11159.2	99.8
0°-90°	11178.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11178.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18344	
5°	17512	###
15°	12618	3505
25°	7879	3574
35°	3173	2002
45°	474	427
55°	40	53
65°	16	14
75°	5	3
85°	5	2
90°	0	



TEST NUMBER: P246960

CATALOG NUMBER: LSR8B100D010 EC8B100835 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	18343.5
2.5°	18136.8
5°	17511.8
7.5°	16506.0
10°	15265.0
12.5°	13933.0
15°	12617.9
17.5°	11295.1
20°	10078.8
22.5°	8946.9
25°	7878.7
27.5°	6757.3
30°	5573.5
32.5°	4336.4
35°	3173.3
37.5°	2125.9
40°	1321.6
42.5°	790.1
45°	474.3
47.5°	263.8
50°	154.6
52.5°	81.9
55°	40.3
57.5°	28.6
60°	24.7
62.5°	11.7
65°	15.6
67.5°	15.6
70°	1.3
72.5°	3.9
75°	5.2
77.5°	2.6
80°	0.0
82.5°	1.3
85°	5.2
87.5°	0.0
90°	0.0

(END OF REPORT)