

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250563

Luminaire Tested: **LSR8B100D010 EC8B100840 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100840 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6889.0 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250563

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250563

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275637
5°	267208
10°	234023
15°	206606
20°	189321
25°	174323
30°	145094
35°	96373
40°	46904
45°	16986
50°	5109
55°	360
60°	0
65°	241
70°	0
75°	0
80°	586
85°	0



TEST NUMBER: P250563

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	785.1	11.4
10°-20°	1823.3	26.5
20°-30°	2313.2	33.6
30°-40°	1584.7	23.0
40°-50°	361.1	5.2
50°-60°	18.0	0.3
60°-70°	0.8	0.0
70°-80°	1.3	0.0
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4921.6	71.4
0°-40°	6506.3	94.4
0°-60°	6885.5	99.9
0°-90°	6889.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6889.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8939	
5°	8632	785
15°	6472	1823
25°	5124	2313
35°	2560	1585
45°	390	361
55°	7	18
65°	3	1
75°	0	1
85°	0	1
90°	0	



TEST NUMBER: P250563

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	8938.7
1°	8985.3
2°	8968.6
3°	8902.1
4°	8788.8
5°	8632.4
6°	8442.6
7°	8222.9
8°	7979.9
9°	7720.2
10°	7473.9
11°	7247.5
12°	7004.5
13°	6828.1
14°	6641.6
15°	6471.8
16°	6318.7
17°	6168.8
18°	6029.0
19°	5892.5
20°	5769.3
21°	5642.8
22°	5513.0
23°	5399.9
24°	5273.3
25°	5123.5
26°	4957.0
27°	4764.0
28°	4557.6
29°	4327.9
30°	4074.9
31°	3788.5
32°	3492.3
33°	3182.6
34°	2866.3
35°	2560.1
37.5°	1807.7
40°	1165.2
42.5°	685.8
45°	389.5
47.5°	209.8
50°	106.5
52.5°	20.0
55°	6.7
57.5°	3.3



TEST NUMBER: P250563

CATALOG NUMBER: LSR8B100D010 EC8B100840 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	3.3
67.5°	0.0
70°	0.0
72.5°	3.3
75°	0.0
77.5°	0.0
80°	3.3
82.5°	0.0
85°	0.0
87.5°	3.3
90°	0.0

(END OF REPORT)