

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843887

Luminaire Tested: **LD6C08DE010B35 EU6C08B35 6LBNH**

Issue Date: 2/17/2023



Test Information

Test Method: LM-79-08
Report Number: P843887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B35 EU6C08B35 6LBNH
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.9 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843887

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P843887

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 94 | 98 | 95 | 92 | 95 | 93 | 90 | 92 | 90 | 89 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 95 | 90 | 86 | 92 | 88 | 85 | 90 | 86 | 84 | 87 | 85 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 89 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 83 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 73 | 81 | 76 | 73 | 80 | 75 | 72 | 78 | 74 | 72 | 70 | | | |
| 6 | 88 | 79 | 73 | 69 | 86 | 78 | 72 | 68 | 77 | 72 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 64 | 60 | 68 | 63 | 59 | 67 | 63 | 59 | 66 | 62 | 59 | 58 | | | |
| 9 | 76 | 66 | 60 | 56 | 75 | 66 | 60 | 56 | 65 | 59 | 56 | 64 | 59 | 56 | 63 | 59 | 55 | 54 | | | |
| 10 | 72 | 62 | 57 | 53 | 71 | 62 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 60 | 55 | 52 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 37157 |
| 5° | 36242 |
| 10° | 33438 |
| 15° | 29603 |
| 20° | 25704 |
| 25° | 21987 |
| 30° | 18129 |
| 35° | 11939 |
| 40° | 6419 |
| 45° | 2838 |
| 50° | 1151 |
| 55° | 832 |
| 60° | 537 |
| 65° | 389 |
| 70° | 305 |
| 75° | 212 |
| 80° | 316 |
| 85° | 0 |



TEST NUMBER: P843887

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 61.0 | 11.5 |
| 10°-20° | 145.4 | 27.5 |
| 20°-30° | 166.5 | 31.5 |
| 30°-40° | 111.9 | 21.2 |
| 40°-50° | 32.0 | 6.0 |
| 50°-60° | 7.8 | 1.5 |
| 60°-70° | 3.0 | 0.6 |
| 70°-80° | 1.2 | 0.2 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 372.9 | 70.5 |
| 0°-40° | 484.8 | 91.7 |
| 0°-60° | 524.6 | 99.2 |
| 0°-90° | 528.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 528.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 678 | |
| 5° | 659 | 61 |
| 15° | 522 | 145 |
| 25° | 364 | 167 |
| 35° | 178 | 112 |
| 45° | 37 | 32 |
| 55° | 9 | 8 |
| 65° | 3 | 3 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P843887

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 677.8 |
| 2.5° | 673.1 |
| 5° | 658.6 |
| 7.5° | 632.6 |
| 10° | 600.7 |
| 12.5° | 560.2 |
| 15° | 521.6 |
| 17.5° | 481.2 |
| 20° | 440.6 |
| 22.5° | 402.1 |
| 25° | 363.5 |
| 27.5° | 327.9 |
| 30° | 286.4 |
| 32.5° | 231.4 |
| 35° | 178.4 |
| 37.5° | 130.2 |
| 40° | 89.7 |
| 42.5° | 58.8 |
| 45° | 36.6 |
| 47.5° | 22.2 |
| 50° | 13.5 |
| 52.5° | 10.6 |
| 55° | 8.7 |
| 57.5° | 6.8 |
| 60° | 4.9 |
| 62.5° | 3.8 |
| 65° | 3.0 |
| 67.5° | 1.9 |
| 70° | 1.9 |
| 72.5° | 1.0 |
| 75° | 1.0 |
| 77.5° | 1.0 |
| 80° | 1.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)