

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P843888

Luminaire Tested: **LD6C08DE010B35 EU6C08B35 6LBNLI**

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-08
Report Number: P843888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C08DE010B35 EU6C08B35 6LBNLI
Description:
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 669.5 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P843888

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P843888

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83562
5°	78142
10°	63732
15°	46896
20°	32325
25°	23995
30°	18022
35°	11243
40°	5460
45°	1868
50°	247
55°	182
60°	110
65°	130
70°	160
75°	0
80°	0
85°	0



TEST NUMBER: P843888

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.7	18.9
10°-20°	227.5	34.0
20°-30°	183.9	27.5
30°-40°	106.0	15.8
40°-50°	22.4	3.3
50°-60°	1.9	0.3
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.1	80.4
0°-40°	644.1	96.2
0°-60°	668.4	99.8
0°-90°	669.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1524	
5°	1420	127
15°	826	227
25°	397	184
35°	168	106
45°	24	22
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P843888

CATALOG NUMBER: LD6C08DE010B35 EU6C08B35 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1524.3
2.5°	1506.0
5°	1420.0
7.5°	1296.4
10°	1144.9
12.5°	989.5
15°	826.3
17.5°	669.0
20°	554.1
22.5°	466.3
25°	396.7
27.5°	337.9
30°	284.7
32.5°	225.9
35°	168.0
37.5°	116.8
40°	76.3
42.5°	46.3
45°	24.1
47.5°	9.6
50°	2.9
52.5°	2.9
55°	1.9
57.5°	1.9
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)