

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245526

Luminaire Tested: **LSR8B10D010 EC8B10827 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245526
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10827 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 954.0 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245526

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245526

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22905
5°	22364
10°	21665
15°	21351
20°	21100
25°	20646
30°	19338
35°	15792
40°	9427
45°	5660
50°	4082
55°	2779
60°	1739
65°	854
70°	216
75°	83
80°	53
85°	0



TEST NUMBER: P245526

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.0	7.1
10°-20°	188.7	19.8
20°-30°	277.2	29.1
30°-40°	251.3	26.3
40°-50°	107.6	11.3
50°-60°	47.6	5.0
60°-70°	12.7	1.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.9	56.0
0°-40°	785.1	82.3
0°-60°	940.3	98.6
0°-90°	954.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	954.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	743	
5°	722	68
15°	669	189
25°	607	277
35°	420	251
45°	130	108
55°	52	48
65°	12	13
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245526

CATALOG NUMBER: LSR8B10D010 EC8B10827 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	742.8
2.5°	737.0
5°	722.5
7.5°	706.0
10°	691.9
12.5°	680.2
15°	668.8
17.5°	656.7
20°	643.0
22.5°	626.8
25°	606.8
27.5°	579.9
30°	543.1
32.5°	491.4
35°	419.5
37.5°	325.1
40°	234.2
42.5°	169.1
45°	129.8
47.5°	104.7
50°	85.1
52.5°	67.5
55°	51.7
57.5°	38.6
60°	28.2
62.5°	19.6
65°	11.7
67.5°	5.2
70°	2.4
72.5°	1.4
75°	0.7
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)