

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244890

Luminaire Tested: **LSR8B10D010 EC8B10835 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244890  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10835 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3500 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1212.0 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244890

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244890

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21191
5°	21123
10°	20935
15°	20728
20°	20503
25°	20180
30°	19626
35°	18732
40°	17362
45°	14657
50°	10055
55°	5548
60°	2788
65°	1569
70°	857
75°	608
80°	391
85°	248



TEST NUMBER: P244890

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.7	5.3
10°-20°	183.1	15.1
20°-30°	272.6	22.5
30°-40°	309.7	25.6
40°-50°	253.1	20.9
50°-60°	99.2	8.2
60°-70°	23.1	1.9
70°-80°	5.6	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.4	42.9
0°-40°	830.1	68.5
0°-60°	1182.4	97.6
0°-90°	1212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1212.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	687	
5°	682	65
15°	649	183
25°	593	273
35°	498	310
45°	336	253
55°	103	99
65°	22	23
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P244890

CATALOG NUMBER: LSR8B10D010 EC8B10835 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	687.2
2.5°	686.1
5°	682.4
7.5°	676.2
10°	668.6
12.5°	659.1
15°	649.3
17.5°	637.6
20°	624.8
22.5°	609.9
25°	593.1
27.5°	573.4
30°	551.2
32.5°	526.1
35°	497.6
37.5°	466.3
40°	431.3
42.5°	389.0
45°	336.1
47.5°	274.1
50°	209.6
52.5°	150.6
55°	103.2
57.5°	67.4
60°	45.2
62.5°	31.0
65°	21.5
67.5°	14.2
70°	9.5
72.5°	6.6
75°	5.1
77.5°	3.6
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)