

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247064

Luminaire Tested: **LSR8B100D010 EC8B100850 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247064  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B100D010 EC8B100850 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11735.0 lumens  
Efficiency: N/A  
Efficacy: 110.4 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247064

CATALOG NUMBER: LSR8B100D010 EC8B100850 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P247064

CATALOG NUMBER: LSR8B100D010 EC8B100850 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	201929
5°	205866
10°	214697
15°	226827
20°	235329
25°	237039
30°	225832
35°	199198
40°	160581
45°	114007
50°	68520
55°	30870
60°	7956
65°	1715
70°	847
75°	572
80°	284
85°	0



TEST NUMBER: P247064

CATALOG NUMBER: LSR8B100D010 EC8B100850 8LBWOLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	641.5	5.5
10°-20°	2008.8	17.1
20°-30°	3176.8	27.1
30°-40°	3264.3	27.8
40°-50°	2024.9	17.3
50°-60°	574.1	4.9
60°-70°	38.8	0.3
70°-80°	5.2	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5827.2	49.7
0°-40°	9091.5	77.5
0°-60°	11690.4	99.6
0°-90°	11735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11735.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6548	
5°	6651	642
15°	7105	2009
25°	6967	3177
35°	5292	3264
45°	2614	2025
55°	574	574
65°	24	39
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P247064

CATALOG NUMBER: LSR8B100D010 EC8B100850 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6548.4
2.5°	6560.9
5°	6650.7
7.5°	6756.1
10°	6856.7
12.5°	6981.0
15°	7105.2
17.5°	7176.0
20°	7171.3
22.5°	7102.1
25°	6966.8
27.5°	6721.4
30°	6342.4
32.5°	5843.7
35°	5291.6
37.5°	4667.2
40°	3989.2
42.5°	3284.4
45°	2614.3
47.5°	1991.5
50°	1428.3
52.5°	961.2
55°	574.2
57.5°	295.8
60°	129.0
62.5°	52.0
65°	23.5
67.5°	14.1
70°	9.4
72.5°	6.3
75°	4.8
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)