

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244680

Luminaire Tested: **LSR8B10D010 EC8B10840 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244680  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B10D010 EC8B10840 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1095.0 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244680

CATALOG NUMBER: LSR8B10D010 EC8B10840 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244680

CATALOG NUMBER: LSR8B10D010 EC8B10840 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24472
5°	23977
10°	23218
15°	22906
20°	22771
25°	22480
30°	21271
35°	17546
40°	10957
45°	7043
50°	5464
55°	4204
60°	3188
65°	2072
70°	884
75°	429
80°	195
85°	142



TEST NUMBER: P244680

CATALOG NUMBER: LSR8B10D010 EC8B10840 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.9	6.7
10°-20°	202.7	18.5
20°-30°	301.9	27.6
30°-40°	280.4	25.6
40°-50°	132.4	12.1
50°-60°	71.2	6.5
60°-70°	28.6	2.6
70°-80°	4.5	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.5	52.7
0°-40°	857.9	78.3
0°-60°	1061.5	96.9
0°-90°	1095.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1095.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	794	
5°	775	73
15°	718	203
25°	661	302
35°	466	280
45°	162	132
55°	78	71
65°	28	29
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P244680

CATALOG NUMBER: LSR8B10D010 EC8B10840 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	793.6
2.5°	788.1
5°	774.6
7.5°	757.5
10°	741.5
12.5°	728.4
15°	717.5
17.5°	706.2
20°	693.9
22.5°	679.7
25°	660.7
27.5°	634.2
30°	597.4
32.5°	543.6
35°	466.1
37.5°	367.1
40°	272.2
42.5°	202.7
45°	161.5
47.5°	135.0
50°	113.9
52.5°	95.0
55°	78.2
57.5°	63.7
60°	51.7
62.5°	40.4
65°	28.4
67.5°	16.7
70°	9.8
72.5°	5.8
75°	3.6
77.5°	2.2
80°	1.1
82.5°	0.7
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)