

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250535

Luminaire Tested: **LSR8B100D010 EC8B100930 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250535  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B100D010 EC8B100930 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7860.4 lumens  
Efficiency: N/A  
Efficacy: 73.9 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250535

CATALOG NUMBER: LSR8B100D010 EC8B100930 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250535

CATALOG NUMBER: LSR8B100D010 EC8B100930 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250535

CATALOG NUMBER: LSR8B100D010 EC8B100930 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	887.5	11.3
10°-20°	2110.2	26.8
20°-30°	2629.0	33.4
30°-40°	1773.3	22.6
40°-50°	419.3	5.3
50°-60°	30.7	0.4
60°-70°	5.5	0.1
70°-80°	4.0	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5626.8	71.6
0°-40°	7400.0	94.1
0°-60°	7850.0	99.9
0°-90°	7860.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7860.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9969	
5°	9680	888
15°	7494	2110
25°	5828	2629
35°	2842	1773
45°	456	419
55°	14	31
65°	0	5
75°	10	4
85°	3	1
90°	0	



TEST NUMBER: P250535

CATALOG NUMBER: LSR8B100D010 EC8B100930 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9969.2
2.5°	9952.1
5°	9680.1
7.5°	9187.0
10°	8578.5
12.5°	8003.8
15°	7493.9
17.5°	7055.2
20°	6650.7
22.5°	6263.0
25°	5827.9
27.5°	5260.1
30°	4566.3
32.5°	3726.5
35°	2842.5
37.5°	2033.3
40°	1326.0
42.5°	792.2
45°	455.6
47.5°	255.0
50°	125.8
52.5°	57.8
55°	13.6
57.5°	3.4
60°	6.8
62.5°	10.2
65°	0.0
67.5°	6.8
70°	3.4
72.5°	3.4
75°	10.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	3.4
87.5°	0.0
90°	0.0

(END OF REPORT)