

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245622

Luminaire Tested: **LSR8B10D010 EC8B10850 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201794)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10850 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 2183 (1 lamp)
Luminaire Lumens: 950.0 lumens
Efficiency: 43.5%
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245622

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245622

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	52	52	52	52	51	51	51	51	48	48	48	46	46	46	44	44	44	44
1	50	48	47	47	49	48	47	46	46	45	44	44	44	43	43	42	42	41
2	47	45	44	42	46	45	43	42	43	42	41	42	41	40	41	40	39	39
3	45	43	41	39	44	42	40	39	41	39	38	40	39	38	39	38	37	36
4	43	40	38	36	42	40	38	36	39	37	36	38	36	35	37	36	35	34
5	41	38	35	34	41	37	35	34	37	35	33	36	34	33	35	34	33	32
6	39	36	33	32	39	35	33	32	35	33	31	34	32	31	34	32	31	30
7	38	34	31	30	37	34	31	30	33	31	29	33	31	29	32	30	29	29
8	36	32	30	28	35	32	30	28	31	29	28	31	29	28	31	29	28	27
9	34	30	28	26	34	30	28	26	30	28	26	29	28	26	29	27	26	26
10	33	29	27	25	32	29	27	25	28	26	25	28	26	25	28	26	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46773
5°	46023
10°	40890
15°	33737
20°	28402
25°	23963
30°	17939
35°	10145
40°	4005
45°	1082
50°	206
55°	0
60°	25
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245622

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBN0GPH

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	136.0	14.3	6.2	0°	1517	
10°-20°	296.5	31.2	13.6	5°	1487	136
20°-30°	317.6	33.4	14.6	15°	1057	297
30°-40°	172.1	18.1	7.9	25°	704	318
40°-50°	26.8	2.8	1.2	35°	270	172
50°-60°	0.7	0.1	0.0	45°	25	27
60°-70°	0.1	0.0	0.0	55°	0	1
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	750.2	79.0	34.4	165°	0	0
0°-40°	922.3	97.1	42.3	175°	0	0
0°-60°	949.8	100.0	43.5	180°	0	0
0°-90°	950.0	100.0	43.5			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	950.0	100.0	43.5			



TEST NUMBER: P245622

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1516.8
2.5°	1515.5
5°	1486.8
7.5°	1415.9
10°	1305.9
12.5°	1177.2
15°	1056.8
17.5°	954.7
20°	865.5
22.5°	785.6
25°	704.3
27.5°	612.1
30°	503.8
32.5°	384.3
35°	269.5
37.5°	172.6
40°	99.5
42.5°	53.0
45°	24.8
47.5°	13.5
50°	4.3
52.5°	0.4
55°	0.0
57.5°	0.4
60°	0.4
62.5°	0.0
65°	0.0
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245622

CATALOG NUMBER: LSR8B10D010 EC8B10850 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)