

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243930

Luminaire Tested: **LSR8B10D010 EC8B10927 8LBN0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B10927 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 867.4 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243930

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243930

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBNOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131042
5°	91014
10°	47895
15°	30302
20°	22518
25°	17703
30°	12747
35°	5473
40°	1908
45°	733
50°	168
55°	59
60°	0
65°	80
70°	27
75°	71
80°	107
85°	0



TEST NUMBER: P243930

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBNOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.7	27.2
10°-20°	273.9	31.6
20°-30°	236.4	27.3
30°-40°	102.6	11.8
40°-50°	16.1	1.9
50°-60°	1.2	0.1
60°-70°	0.6	0.1
70°-80°	0.7	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.0	86.0
0°-40°	848.5	97.8
0°-60°	865.8	99.8
0°-90°	867.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	867.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4250	
5°	2940	236
15°	949	274
25°	520	236
35°	145	103
45°	17	16
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243930

CATALOG NUMBER: LSR8B10D010 EC8B10927 8LBNOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4249.6
2.5°	3837.5
5°	2940.3
7.5°	2097.0
10°	1529.6
12.5°	1173.6
15°	949.2
17.5°	798.3
20°	686.2
22.5°	590.6
25°	520.3
27.5°	446.2
30°	358.0
32.5°	248.8
35°	145.4
37.5°	81.2
40°	47.4
42.5°	29.4
45°	16.8
47.5°	13.5
50°	3.5
52.5°	1.8
55°	1.1
57.5°	0.6
60°	0.0
62.5°	0.3
65°	1.1
67.5°	0.9
70°	0.3
72.5°	1.5
75°	0.6
77.5°	0.0
80°	0.6
82.5°	0.3
85°	0.0
87.5°	0.6
90°	0.0

(END OF REPORT)