

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244800

Luminaire Tested: **LSR8B10D010 EC8B109730 8LBNOWMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B10D010 EC8B109730 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 749.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244800

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244800

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88	88	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82	82	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77	77	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72	72	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68	68	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64	64	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60	60	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	59	65	61	58	57	57	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54	54	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244800

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	13.2
10°-20°	227.4	30.4
20°-30°	241.3	32.2
30°-40°	137.7	18.4
40°-50°	34.1	4.6
50°-60°	6.7	0.9
60°-70°	2.0	0.3
70°-80°	0.4	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.7	75.8
0°-40°	705.3	94.2
0°-60°	746.2	99.6
0°-90°	749.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	749.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1091	
5°	1072	99
15°	816	227
25°	533	241
35°	215	138
45°	39	34
55°	6	7
65°	2	2
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244800

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1090.8
2.5°	1090.3
5°	1071.5
7.5°	1030.2
10°	969.2
12.5°	895.5
15°	816.2
17.5°	740.5
20°	668.6
22.5°	599.4
25°	532.7
27.5°	461.0
30°	381.9
32.5°	296.8
35°	215.3
37.5°	148.3
40°	95.9
42.5°	60.8
45°	38.6
47.5°	25.2
50°	15.8
52.5°	9.6
55°	6.2
57.5°	5.0
60°	3.2
62.5°	3.0
65°	1.5
67.5°	1.5
70°	1.2
72.5°	0.7
75°	0.0
77.5°	0.2
80°	0.2
82.5°	0.5
85°	0.5
87.5°	0.2
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244800

CATALOG NUMBER: LSR8B10D010 EC8B109730 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)