

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250353

Luminaire Tested: **LSR8B100D010 EC8B100950 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100950 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8130.0 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250353

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250353

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	400591
5°	394191
10°	350231
15°	288910
20°	243319
25°	205227
30°	153661
35°	86962
40°	34385
45°	9232
50°	1770
55°	0
60°	253
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250353

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1166.2	14.3
10°-20°	2534.7	31.2
20°-30°	2721.1	33.5
30°-40°	1470.7	18.1
40°-50°	229.5	2.8
50°-60°	6.3	0.1
60°-70°	1.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6422.0	79.0
0°-40°	7892.7	97.1
0°-60°	8128.4	100.0
0°-90°	8130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8130.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12991	
5°	12735	###
15°	9050	2535
25°	6032	2721
35°	2310	1471
45°	212	229
55°	0	6
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250353

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	12990.9
1°	13015.6
2°	13003.4
3°	12958.8
4°	12873.3
5°	12734.7
6°	12544.0
7°	12287.3
8°	11966.1
9°	11596.3
10°	11185.2
11°	10753.9
12°	10306.5
13°	9859.6
14°	9444.3
15°	9049.9
16°	8687.8
17°	8338.0
18°	8012.6
19°	7707.9
20°	7414.8
21°	7130.0
22°	6861.4
23°	6593.3
24°	6312.7
25°	6031.8
26°	5747.0
27°	5421.8
28°	5063.7
29°	4698.1
30°	4315.5
31°	3904.8
32°	3493.6
33°	3087.1
34°	2676.3
35°	2310.1
37.5°	1476.4
40°	854.2
42.5°	455.7
45°	211.7
47.5°	114.1
50°	36.9
52.5°	4.1
55°	0.0
57.5°	4.1



TEST NUMBER: P250353

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
60°	4.1
62.5°	0.0
65°	0.0
67.5°	4.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)