

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247036

Luminaire Tested: **LSR8B100D010 EC8B100950 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-80)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B100950 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9548.0 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.56
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247036

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247036

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	105	102	99	107	104	100	98	100	98	96	98	95	94	95	93	92	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	85
4	101	94	90	86	99	93	89	85	91	87	84	89	86	83	87	85	83	81
5	97	90	85	81	95	89	84	80	87	83	80	85	82	79	84	81	78	77
6	93	85	80	76	91	84	80	76	83	79	76	82	78	75	80	77	75	73
7	89	81	76	72	88	81	76	72	79	75	72	78	74	72	77	74	71	70
8	86	78	72	69	85	77	72	69	76	72	69	75	71	68	74	71	68	67
9	82	74	69	66	81	74	69	66	73	69	65	72	68	65	71	68	65	64
10	79	71	66	63	79	71	66	63	70	66	63	69	65	62	69	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	747953
5°	708159
10°	533328
15°	370703
20°	276341
25°	208000
30°	139087
35°	72800
40°	28121
45°	10396
50°	2643
55°	516
60°	74
65°	263
70°	325
75°	0
80°	0
85°	425



TEST NUMBER: P247036

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1989.3	20.8
10°-20°	3289.9	34.5
20°-30°	2773.5	29.0
30°-40°	1258.5	13.2
40°-50°	219.7	2.3
50°-60°	12.0	0.1
60°-70°	1.8	0.0
70°-80°	2.0	0.0
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8052.7	84.3
0°-40°	9311.2	97.5
0°-60°	9542.9	99.9
0°-90°	9548.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9548.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24256	
5°	22878	###
15°	11612	3290
25°	6113	2774
35°	1934	1259
45°	238	220
55°	10	12
65°	4	2
75°	0	2
85°	1	1
90°	0	



TEST NUMBER: P247036

CATALOG NUMBER: LSR8B100D010 EC8B100950 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	24255.6
2.5°	24041.2
5°	22877.7
7.5°	20343.4
10°	17032.7
12.5°	13972.5
15°	11612.0
17.5°	9838.6
20°	8421.1
22.5°	7173.8
25°	6113.3
27.5°	5034.9
30°	3906.2
32.5°	2843.4
35°	1933.9
37.5°	1187.4
40°	698.6
42.5°	409.8
45°	238.4
47.5°	142.6
50°	55.1
52.5°	8.4
55°	9.6
57.5°	8.4
60°	1.2
62.5°	1.2
65°	3.6
67.5°	0.0
70°	3.6
72.5°	6.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.2
87.5°	3.6
90°	0.0

(END OF REPORT)