

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243877

Luminaire Tested: **LSR8B15D010 EC8B15830 8LBN0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243877  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15830 8LBNOLI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1443.0 lumens  
Efficiency: N/A  
Efficacy: 100.2 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243877

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243877

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBNOLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	218003
5°	151415
10°	79680
15°	50415
20°	37465
25°	29455
30°	21204
35°	9099
40°	3172
45°	1217
50°	283
55°	108
60°	0
65°	146
70°	45
75°	119
80°	178
85°	0



TEST NUMBER: P243877

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBNOLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	392.2	27.2
10°-20°	455.6	31.6
20°-30°	393.3	27.3
30°-40°	170.6	11.8
40°-50°	26.7	1.9
50°-60°	1.9	0.1
60°-70°	1.1	0.1
70°-80°	1.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1241.1	86.0
0°-40°	1411.7	97.8
0°-60°	1440.3	99.8
0°-90°	1443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1443.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7070	
5°	4892	392
15°	1579	456
25°	866	393
35°	242	171
45°	28	27
55°	2	2
65°	2	1
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P243877

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBNOLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7069.7
2.5°	6384.2
5°	4891.6
7.5°	3488.6
10°	2544.7
12.5°	1952.5
15°	1579.2
17.5°	1328.1
20°	1141.7
22.5°	982.6
25°	865.7
27.5°	742.4
30°	595.5
32.5°	414.0
35°	241.7
37.5°	135.1
40°	78.8
42.5°	48.9
45°	27.9
47.5°	22.5
50°	5.9
52.5°	2.9
55°	2.0
57.5°	1.0
60°	0.0
62.5°	0.5
65°	2.0
67.5°	1.5
70°	0.5
72.5°	2.4
75°	1.0
77.5°	0.0
80°	1.0
82.5°	0.5
85°	0.0
87.5°	1.0
90°	0.0

(END OF REPORT)