

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244315

Luminaire Tested: **LSR8B15D010 EC8B15835 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15835 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1416.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244315

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P244315

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66653
5°	62171
10°	53591
15°	46379
20°	40346
25°	34674
30°	27243
35°	15897
40°	7334
45°	3794
50°	1905
55°	925
60°	475
65°	277
70°	126
75°	119
80°	89
85°	0



TEST NUMBER: P244315

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.8	12.8
10°-20°	406.2	28.7
20°-30°	461.8	32.6
30°-40°	271.2	19.2
40°-50°	72.8	5.1
50°-60°	17.3	1.2
60°-70°	3.9	0.3
70°-80°	0.9	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.8	74.1
0°-40°	1321.1	93.3
0°-60°	1411.1	99.7
0°-90°	1416.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1416.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2162	
5°	2008	182
15°	1453	406
25°	1019	462
35°	422	271
45°	87	73
55°	17	17
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244315

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2161.5
1°	2149.6
2°	2127.6
3°	2096.5
4°	2056.3
5°	2008.5
6°	1954.5
7°	1893.3
8°	1832.0
9°	1770.4
10°	1711.5
11°	1654.1
12°	1600.1
13°	1549.9
14°	1499.7
15°	1452.8
16°	1406.9
17°	1361.5
18°	1317.5
19°	1273.0
20°	1229.5
21°	1186.0
22°	1144.4
23°	1103.2
24°	1061.2
25°	1019.1
26°	975.6
27°	928.2
28°	878.5
29°	824.0
30°	765.1
32.5°	600.2
35°	422.3
37.5°	278.3
40°	182.2
42.5°	125.8
45°	87.0
47.5°	59.8
50°	39.7
52.5°	25.8
55°	17.2
57.5°	11.5
60°	7.7
62.5°	5.3
65°	3.8



TEST NUMBER: P244315

CATALOG NUMBER: LSR8B15D010 EC8B15835 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	2.4
70°	1.4
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)