

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247764

Luminaire Tested: **LSR8B100D010 EC8B1009730 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B100D010 EC8B1009730 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8869.0 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247764

CATALOG NUMBER: LSR8B100D010 EC8B1009730 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P247764

CATALOG NUMBER: LSR8B100D010 EC8B1009730 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58	67	61	57	65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47	57	51	46	55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247764

CATALOG NUMBER: LSR8B100D010 EC8B1009730 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.1	5.0
10°-20°	1253.7	14.1
20°-30°	1844.5	20.8
30°-40°	2083.4	23.5
40°-50°	1754.6	19.8
50°-60°	885.2	10.0
60°-70°	346.8	3.9
70°-80°	195.8	2.2
80°-90°	60.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3542.3	39.9
0°-40°	5625.7	63.4
0°-60°	8265.5	93.2
0°-90°	8869.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8869.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4710	
5°	4680	444
15°	4457	1254
25°	4014	1844
35°	3346	2083
45°	2311	1755
55°	955	885
65°	336	347
75°	190	196
85°	55	61
90°	0	



TEST NUMBER: P247764

CATALOG NUMBER: LSR8B100D010 EC8B1009730 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4709.5
2.5°	4704.7
5°	4679.9
7.5°	4647.3
10°	4591.8
12.5°	4522.9
15°	4456.8
17.5°	4356.3
20°	4255.8
22.5°	4146.7
25°	4013.6
27.5°	3863.4
30°	3706.4
32.5°	3530.2
35°	3346.5
37.5°	3135.9
40°	2922.4
42.5°	2631.4
45°	2310.7
47.5°	1943.2
50°	1579.4
52.5°	1251.1
55°	955.3
57.5°	719.8
60°	541.8
62.5°	413.5
65°	336.0
67.5°	273.8
70°	222.1
72.5°	214.4
75°	190.5
77.5°	158.9
80°	134.0
82.5°	85.2
85°	54.6
87.5°	17.2
90°	0.0

(END OF REPORT)