

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250550

Luminaire Tested: **LSR8B120D010 EC8B120830 8LBM0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120830 8LBM0B
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7559.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250550

CATALOG NUMBER: LSR8B120D010 EC8B120830 8LBM0B

Luminous Intensity Polar Plot





TEST NUMBER: P250550

CATALOG NUMBER: LSR8B120D010 EC8B120830 8LBM0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	302446
5°	293197
10°	256780
15°	226703
20°	207737
25°	191277
30°	159205
35°	105743
40°	51465
45°	18639
50°	5608
55°	392
60°	0
65°	270
70°	0
75°	0
80°	657
85°	0



TEST NUMBER: P250550

CATALOG NUMBER: LSR8B120D010 EC8B120830 8LBM0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	861.5	11.4
10°-20°	2000.7	26.5
20°-30°	2538.2	33.6
30°-40°	1738.8	23.0
40°-50°	396.3	5.2
50°-60°	19.8	0.3
60°-70°	0.9	0.0
70°-80°	1.5	0.0
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5400.3	71.4
0°-40°	7139.1	94.4
0°-60°	7555.1	99.9
0°-90°	7559.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7559.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9808	
5°	9472	861
15°	7101	2001
25°	5622	2538
35°	2809	1739
45°	427	396
55°	7	20
65°	4	1
75°	0	1
85°	0	2
90°	0	



TEST NUMBER: P250550

CATALOG NUMBER: LSR8B120D010 EC8B120830 8LBM0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	9808.1
1°	9859.2
2°	9840.9
3°	9767.8
4°	9643.6
5°	9472.0
6°	9263.7
7°	9022.7
8°	8756.0
9°	8471.0
10°	8200.7
11°	7952.3
12°	7685.7
13°	7492.1
14°	7287.5
15°	7101.3
16°	6933.2
17°	6768.8
18°	6615.4
19°	6465.6
20°	6330.5
21°	6191.6
22°	6049.2
23°	5925.0
24°	5786.2
25°	5621.8
26°	5439.2
27°	5227.3
28°	5000.8
29°	4748.8
30°	4471.2
31°	4157.0
32°	3831.9
33°	3492.2
34°	3145.1
35°	2809.0
37.5°	1983.5
40°	1278.5
42.5°	752.5
45°	427.4
47.5°	230.2
50°	116.9
52.5°	21.9
55°	7.3
57.5°	3.7



TEST NUMBER: P250550

CATALOG NUMBER: LSR8B120D010 EC8B120830 8LBM0B

CANDELA DISTRIBUTION (continued):

	0°
60°	0.0
62.5°	0.0
65°	3.7
67.5°	0.0
70°	0.0
72.5°	3.7
75°	0.0
77.5°	0.0
80°	3.7
82.5°	0.0
85°	0.0
87.5°	3.7
90°	0.0

(END OF REPORT)