

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244039

Luminaire Tested: **LSR8B15D010 EC8B15850 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15850 8LBS0LI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1748.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244039

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBS0LI

Luminous Intensity Polar Plot





TEST NUMBER: P244039

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30053
5°	30183
10°	30673
15°	31448
20°	31998
25°	32034
30°	31042
35°	28421
40°	24700
45°	19546
50°	12674
55°	6333
60°	2658
65°	1167
70°	361
75°	179
80°	178
85°	177



TEST NUMBER: P244039

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBS0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	5.3
10°-20°	278.4	15.9
20°-30°	431.2	24.7
30°-40°	468.3	26.8
40°-50°	340.3	19.5
50°-60°	115.7	6.6
60°-70°	18.4	1.1
70°-80°	2.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.8	45.9
0°-40°	1271.2	72.7
0°-60°	1727.2	98.8
0°-90°	1748.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1748.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	975	
5°	975	93
15°	985	278
25°	942	431
35°	755	468
45°	448	340
55°	118	116
65°	16	18
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244039

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBS0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	974.6
2.5°	974.6
5°	975.1
7.5°	976.6
10°	979.6
12.5°	983.1
15°	985.1
17.5°	983.1
20°	975.1
22.5°	960.6
25°	941.5
27.5°	912.9
30°	871.8
32.5°	817.2
35°	755.0
37.5°	687.3
40°	613.6
42.5°	533.9
45°	448.2
47.5°	356.0
50°	264.2
52.5°	181.0
55°	117.8
57.5°	71.7
60°	43.1
62.5°	26.6
65°	16.0
67.5°	9.0
70°	4.0
72.5°	2.5
75°	1.5
77.5°	1.0
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)