

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244939

Luminaire Tested: **LSR8B15D010 EC8B15927 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244939  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15927 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1285.8 lumens  
Efficiency: N/A  
Efficacy: 89.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244939

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244939

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244939

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	5.3
10°-20°	194.3	15.1
20°-30°	289.2	22.5
30°-40°	328.6	25.6
40°-50°	268.5	20.9
50°-60°	105.3	8.2
60°-70°	24.5	1.9
70°-80°	5.9	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.1	42.9
0°-40°	880.7	68.5
0°-60°	1254.5	97.6
0°-90°	1285.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1285.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	729	
5°	724	69
15°	689	194
25°	629	289
35°	528	329
45°	357	269
55°	110	105
65°	23	24
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P244939

CATALOG NUMBER: LSR8B15D010 EC8B15927 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	729.1
2.5°	727.9
5°	724.1
7.5°	717.4
10°	709.3
12.5°	699.3
15°	688.8
17.5°	676.5
20°	663.0
22.5°	647.1
25°	629.3
27.5°	608.4
30°	584.8
32.5°	558.1
35°	528.0
37.5°	494.7
40°	457.5
42.5°	412.6
45°	356.6
47.5°	290.8
50°	222.4
52.5°	159.8
55°	109.5
57.5°	71.6
60°	47.9
62.5°	32.8
65°	22.8
67.5°	15.1
70°	10.0
72.5°	7.0
75°	5.4
77.5°	3.8
80°	2.4
82.5°	1.1
85°	0.8
87.5°	0.3
90°	0.0

(END OF REPORT)