

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243841

Luminaire Tested: **LSR8B15D010 EC8B15935 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15935 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1387.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243841

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243841

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24607
5°	25336
10°	27448
15°	30031
20°	31243
25°	31129
30°	29198
35°	24484
40°	17048
45°	9764
50°	5243
55°	2161
60°	537
65°	139
70°	72
75°	48
80°	71
85°	0



TEST NUMBER: P243841

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	5.8
10°-20°	265.1	19.1
20°-30°	417.2	30.1
30°-40°	396.8	28.6
40°-50°	182.9	13.2
50°-60°	41.6	3.0
60°-70°	2.7	0.2
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	762.3	55.0
0°-40°	1159.2	83.6
0°-60°	1383.7	99.8
0°-90°	1387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	798	
5°	818	80
15°	941	265
25°	915	417
35°	650	397
45°	224	183
55°	40	42
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P243841

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	798.0
1°	797.7
2°	799.2
3°	803.7
4°	810.6
5°	818.5
6°	828.4
7°	839.0
8°	850.0
9°	862.9
10°	876.6
11°	890.2
12°	904.7
13°	918.3
14°	930.9
15°	940.7
16°	947.9
17°	952.9
18°	955.1
19°	954.8
20°	952.1
21°	947.5
22°	941.9
23°	934.3
24°	925.5
25°	914.9
26°	902.4
27°	886.5
28°	867.5
29°	845.5
30°	820.0
32.5°	743.8
35°	650.4
37.5°	541.9
40°	423.5
42.5°	313.1
45°	223.9
47.5°	158.6
50°	109.3
52.5°	69.8
55°	40.2
57.5°	20.1
60°	8.7
62.5°	3.4
65°	1.9



TEST NUMBER: P243841

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.1
70°	0.8
72.5°	0.8
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)