

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244705

Luminaire Tested: **LSR8B15D010 EC8B15935 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244705  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15935 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1273.0 lumens  
Efficiency: N/A  
Efficacy: 88.4 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244705

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244705

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28450
5°	27877
10°	26994
15°	26628
20°	26472
25°	26137
30°	24732
35°	20399
40°	12736
45°	8190
50°	6352
55°	4887
60°	3707
65°	2408
70°	1028
75°	500
80°	231
85°	142



TEST NUMBER: P244705

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.7	6.7
10°-20°	235.7	18.5
20°-30°	351.0	27.6
30°-40°	326.0	25.6
40°-50°	154.0	12.1
50°-60°	82.7	6.5
60°-70°	33.2	2.6
70°-80°	5.2	0.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.4	52.7
0°-40°	997.4	78.3
0°-60°	1234.1	96.9
0°-90°	1273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1273.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	923	
5°	901	85
15°	834	236
25°	768	351
35°	542	326
45°	188	154
55°	91	83
65°	33	33
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P244705

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	922.6
2.5°	916.2
5°	900.6
7.5°	880.7
10°	862.1
12.5°	846.8
15°	834.1
17.5°	821.0
20°	806.7
22.5°	790.2
25°	768.2
27.5°	737.3
30°	694.6
32.5°	632.0
35°	541.9
37.5°	426.8
40°	316.4
42.5°	235.6
45°	187.8
47.5°	156.9
50°	132.4
52.5°	110.4
55°	90.9
57.5°	74.0
60°	60.1
62.5°	47.0
65°	33.0
67.5°	19.5
70°	11.4
72.5°	6.8
75°	4.2
77.5°	2.5
80°	1.3
82.5°	0.8
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)