

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250305

Luminaire Tested: **LSR8B120D010 EC8B120835 8LBN0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250305  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B120D010 EC8B120835 8LBN0GPH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3500 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9995.0 lumens  
Efficiency: N/A  
Efficacy: 84.5 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250305

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250305

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	492487
5°	484617
10°	430572
15°	355184
20°	299138
25°	252306
30°	188911
35°	106909
40°	42275
45°	11347
50°	2173
55°	0
60°	315
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250305

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1433.7	14.3
10°-20°	3116.1	31.2
20°-30°	3345.4	33.5
30°-40°	1808.1	18.1
40°-50°	282.1	2.8
50°-60°	7.7	0.1
60°-70°	1.9	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7895.2	79.0
0°-40°	9703.3	97.1
0°-60°	9993.1	100.0
0°-90°	9995.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9995.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15971	
5°	15656	###
15°	11126	3116
25°	7416	3345
35°	2840	1808
45°	260	282
55°	0	8
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250305

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15971.0
1°	16001.3
2°	15986.3
3°	15931.6
4°	15826.4
5°	15656.0
6°	15421.5
7°	15106.0
8°	14711.0
9°	14256.5
10°	13751.0
11°	13220.9
12°	12670.8
13°	12121.3
14°	11610.8
15°	11125.9
16°	10680.8
17°	10250.7
18°	9850.7
19°	9476.1
20°	9115.8
21°	8765.6
22°	8435.3
23°	8105.8
24°	7760.8
25°	7415.5
26°	7065.4
27°	6665.6
28°	6225.3
29°	5775.8
30°	5305.5
31°	4800.6
32°	4295.1
33°	3795.2
34°	3290.3
35°	2840.0
37.5°	1815.1
40°	1050.2
42.5°	560.2
45°	260.2
47.5°	140.3
50°	45.3
52.5°	5.1
55°	0.0
57.5°	5.1



TEST NUMBER: P250305

CATALOG NUMBER: LSR8B120D010 EC8B120835 8LBN0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	5.1
62.5°	0.0
65°	0.0
67.5°	5.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)