

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247761

Luminaire Tested: **LSR8B120D010 EC8B120927 8LBS0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-88)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B120D010 EC8B120927 8LBS0MW
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10690.9 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBS0MW

Luminous Intensity Polar Plot





TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBS0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	62	58	67	61	57	65	60	57	55
6	77	66	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	47	57	51	46	55	50	46	44
8	67	55	48	43	66	55	47	42	53	47	42	52	46	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	60	47	40	36	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBS0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.3	5.0
10°-20°	1511.3	14.1
20°-30°	2223.4	20.8
30°-40°	2511.3	23.5
40°-50°	2115.0	19.8
50°-60°	1067.1	10.0
60°-70°	418.0	3.9
70°-80°	236.1	2.2
80°-90°	73.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4270.0	39.9
0°-40°	6781.3	63.4
0°-60°	9963.3	93.2
0°-90°	10690.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10690.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5677	
5°	5641	535
15°	5372	1511
25°	4838	2223
35°	4034	2511
45°	2785	2115
55°	1152	1067
65°	405	418
75°	230	236
85°	66	73
90°	0	



TEST NUMBER: P247761

CATALOG NUMBER: LSR8B120D010 EC8B120927 8LBS0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5677.0
2.5°	5671.2
5°	5641.2
7.5°	5601.9
10°	5535.0
12.5°	5452.0
15°	5372.3
17.5°	5251.2
20°	5130.0
22.5°	4998.5
25°	4838.1
27.5°	4656.9
30°	4467.7
32.5°	4255.4
35°	4033.9
37.5°	3780.0
40°	3522.7
42.5°	3171.9
45°	2785.4
47.5°	2342.4
50°	1903.8
52.5°	1508.1
55°	1151.6
57.5°	867.7
60°	653.1
62.5°	498.5
65°	405.0
67.5°	330.0
70°	267.8
72.5°	258.4
75°	229.6
77.5°	191.6
80°	161.5
82.5°	102.7
85°	65.8
87.5°	20.8
90°	0.0

(END OF REPORT)