

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244082

Luminaire Tested: **LSR8B20D010 EC8B209730 8LBSOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B20D010 EC8B209730 8LBSOLI
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1806.0 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244082

CATALOG NUMBER: LSR8B20D010 EC8B209730 8LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P244082

CATALOG NUMBER: LSR8B20D010 EC8B209730 8LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244082

CATALOG NUMBER: LSR8B20D010 EC8B209730 8LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.3	5.3
10°-20°	287.6	15.9
20°-30°	445.6	24.7
30°-40°	483.9	26.8
40°-50°	351.6	19.5
50°-60°	119.5	6.6
60°-70°	19.0	1.1
70°-80°	2.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	829.5	45.9
0°-40°	1313.4	72.7
0°-60°	1784.5	98.8
0°-90°	1806.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1806.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1007	
5°	1008	96
15°	1018	288
25°	973	446
35°	780	484
45°	463	352
55°	122	120
65°	17	19
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244082

CATALOG NUMBER: LSR8B20D010 EC8B209730 8LBSOLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1006.9
2.5°	1006.9
5°	1007.5
7.5°	1009.0
10°	1012.1
12.5°	1015.8
15°	1017.8
17.5°	1015.8
20°	1007.5
22.5°	992.4
25°	972.8
27.5°	943.2
30°	900.8
32.5°	844.3
35°	780.1
37.5°	710.1
40°	634.0
42.5°	551.6
45°	463.1
47.5°	367.8
50°	273.0
52.5°	187.0
55°	121.7
57.5°	74.1
60°	44.5
62.5°	27.5
65°	16.6
67.5°	9.3
70°	4.1
72.5°	2.6
75°	1.6
77.5°	1.0
80°	1.0
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)