

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245319

Luminaire Tested: **LSR8B30D010 EC8B30830 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245319  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30830 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 3000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3322.0 lumens  
Efficiency: N/A  
Efficacy: 122.6 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245319

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245319

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58022
5°	58243
10°	58976
15°	60129
20°	60987
25°	61240
30°	59364
35°	54181
40°	46872
45°	36898
50°	23799
55°	11682
60°	4804
65°	2101
70°	604
75°	226
80°	178
85°	0



TEST NUMBER: P245319

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.7	5.4
10°-20°	532.3	16.0
20°-30°	824.1	24.8
30°-40°	892.8	26.9
40°-50°	642.4	19.3
50°-60°	215.0	6.5
60°-70°	32.5	1.0
70°-80°	2.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1536.1	46.2
0°-40°	2428.9	73.1
0°-60°	3286.3	98.9
0°-90°	3322.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3322.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1882	
5°	1882	180
15°	1884	532
25°	1800	824
35°	1439	893
45°	846	642
55°	217	215
65°	29	32
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245319

CATALOG NUMBER: LSR8B30D010 EC8B30830 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1881.6
2.5°	1881.6
5°	1881.6
7.5°	1882.6
10°	1883.5
12.5°	1885.5
15°	1883.5
17.5°	1875.9
20°	1858.5
22.5°	1832.6
25°	1799.9
27.5°	1748.0
30°	1667.2
32.5°	1561.4
35°	1439.3
37.5°	1307.6
40°	1164.4
42.5°	1010.5
45°	846.1
47.5°	668.2
50°	496.1
52.5°	340.4
55°	217.3
57.5°	129.8
60°	77.9
62.5°	47.1
65°	28.8
67.5°	14.4
70°	6.7
72.5°	2.9
75°	1.9
77.5°	1.9
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)