

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246261

Luminaire Tested: **LSR8B30D010 EC8B30835 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30835 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1969.0 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246261

CATALOG NUMBER: LSR8B30D010 EC8B30835 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246261

CATALOG NUMBER: LSR8B30D010 EC8B30835 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55524
5°	54126
10°	52686
15°	51704
20°	50358
25°	48576
30°	44569
35°	34173
40°	16259
45°	6192
50°	3022
55°	1237
60°	308
65°	73
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246261

CATALOG NUMBER: LSR8B30D010 EC8B30835 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.8	8.4
10°-20°	455.8	23.1
20°-30°	650.8	33.1
30°-40°	539.3	27.4
40°-50°	133.0	6.8
50°-60°	23.9	1.2
60°-70°	1.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1271.4	64.6
0°-40°	1810.7	92.0
0°-60°	1967.7	99.9
0°-90°	1969.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1969.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1801	
5°	1749	165
15°	1620	456
25°	1428	651
35°	908	539
45°	142	133
55°	23	24
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246261

CATALOG NUMBER: LSR8B30D010 EC8B30835 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1800.6
2.5°	1785.6
5°	1748.6
7.5°	1712.6
10°	1682.6
12.5°	1653.6
15°	1619.6
17.5°	1579.6
20°	1534.6
22.5°	1483.6
25°	1427.7
27.5°	1351.7
30°	1251.7
32.5°	1110.7
35°	907.8
37.5°	655.8
40°	403.9
42.5°	234.9
45°	142.0
47.5°	94.0
50°	63.0
52.5°	41.0
55°	23.0
57.5°	11.0
60°	5.0
62.5°	2.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)