

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244827

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBM0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244827  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30840 8LBM0WMH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2939.0 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244827

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBM0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244827

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBM0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98  | 98  | 97  | 96  | 94  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  | 96  | 93  | 91  | 93  | 91  | 89  | 88  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  | 93  | 89  | 86  | 90  | 87  | 85  | 88  | 86  | 83  | 82  |
| 4   | 98  | 91  | 85  | 81  | 96  | 89  | 84  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 83  | 80  | 78  | 76  |
| 5   | 93  | 85  | 79  | 75  | 92  | 84  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 73  | 79  | 76  | 73  | 71  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |
| 7   | 84  | 75  | 69  | 65  | 83  | 75  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 71  | 67  | 64  | 63  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 60  | 59  |
| 9   | 77  | 67  | 61  | 58  | 76  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 113767 |
| 5°  | 115954 |
| 10° | 110553 |
| 15° | 97618  |
| 20° | 84595  |
| 25° | 71481  |
| 30° | 53716  |
| 35° | 35969  |
| 40° | 20143  |
| 45° | 8089   |
| 50° | 2802   |
| 55° | 774    |
| 60° | 438    |
| 65° | 387    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P244827

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBM0WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 350.5  | 11.9      |
| 10°-20°   | 852.9  | 29.0      |
| 20°-30°   | 946.5  | 32.2      |
| 30°-40°   | 599.6  | 20.4      |
| 40°-50°   | 166.4  | 5.7       |
| 50°-60°   | 19.0   | 0.6       |
| 60°-70°   | 3.8    | 0.1       |
| 70°-80°   | 0.4    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2149.8 | 73.1      |
| 0°-40°    | 2749.4 | 93.5      |
| 0°-60°    | 2934.9 | 99.9      |
| 0°-90°    | 2939.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2939.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | Flux |
|------|------|------|
| 0°   | 3689 |      |
| 5°   | 3746 | 350  |
| 15°  | 3058 | 853  |
| 25°  | 2101 | 946  |
| 35°  | 956  | 600  |
| 45°  | 186  | 166  |
| 55°  | 14   | 19   |
| 65°  | 5    | 4    |
| 75°  | 0    | 0    |
| 85°  | 0    | 0    |
| 90°  | 0    | 0    |
| 95°  | 0    | 0    |
| 105° | 0    | 0    |
| 115° | 0    | 0    |
| 125° | 0    | 0    |
| 135° | 0    | 0    |
| 145° | 0    | 0    |
| 155° | 0    | 0    |
| 165° | 0    | 0    |
| 175° | 0    | 0    |
| 180° | 0    | 0    |



TEST NUMBER: P244827

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBM0WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°     |        |
|--------|--------|
| 0°     | 3689.4 |
| 2.5°   | 3716.7 |
| 5°     | 3746.0 |
| 7.5°   | 3687.6 |
| 10°    | 3530.7 |
| 12.5°  | 3307.0 |
| 15°    | 3057.8 |
| 17.5°  | 2813.1 |
| 20°    | 2577.9 |
| 22.5°  | 2347.1 |
| 25°    | 2100.9 |
| 27.5°  | 1812.9 |
| 30°    | 1508.6 |
| 32.5°  | 1213.8 |
| 35°    | 955.5  |
| 37.5°  | 722.0  |
| 40°    | 500.4  |
| 42.5°  | 311.2  |
| 45°    | 185.5  |
| 47.5°  | 106.7  |
| 50°    | 58.4   |
| 52.5°  | 28.6   |
| 55°    | 14.4   |
| 57.5°  | 10.9   |
| 60°    | 7.1    |
| 62.5°  | 3.8    |
| 65°    | 5.3    |
| 67.5°  | 2.6    |
| 70°    | 0.0    |
| 72.5°  | 0.8    |
| 75°    | 0.0    |
| 77.5°  | 0.8    |
| 80°    | 0.0    |
| 82.5°  | 0.0    |
| 85°    | 0.0    |
| 87.5°  | 0.0    |
| 90°    | 0.0    |
| 92.5°  | 0.0    |
| 95°    | 0.0    |
| 97.5°  | 0.0    |
| 100°   | 0.0    |
| 102.5° | 0.0    |
| 105°   | 0.0    |
| 107.5° | 0.0    |
| 110°   | 0.0    |



TEST NUMBER: P244827

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBM0WMH

**CANDELA DISTRIBUTION (continued):**

|        | 0°  |
|--------|-----|
| 112.5° | 0.0 |
| 115°   | 0.0 |
| 117.5° | 0.0 |
| 120°   | 0.0 |
| 122.5° | 0.0 |
| 125°   | 0.0 |
| 127.5° | 0.0 |
| 130°   | 0.0 |
| 132.5° | 0.0 |
| 135°   | 0.0 |
| 137.5° | 0.0 |
| 140°   | 0.0 |
| 142.5° | 0.0 |
| 145°   | 0.0 |
| 147.5° | 0.0 |
| 150°   | 0.0 |
| 152.5° | 0.0 |
| 155°   | 0.0 |
| 157.5° | 0.0 |
| 160°   | 0.0 |
| 162.5° | 0.0 |
| 165°   | 0.0 |
| 167.5° | 0.0 |
| 170°   | 0.0 |
| 172.5° | 0.0 |
| 175°   | 0.0 |
| 177.5° | 0.0 |
| 180°   | 0.0 |

(END OF REPORT)