

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246483

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30840 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2801.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246483

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246483

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50035
5°	49982
10°	49717
15°	49358
20°	48813
25°	48042
30°	46631
35°	44435
40°	41160
45°	34534
50°	22835
55°	11274
60°	4471
65°	1737
70°	270
75°	0
80°	0
85°	0



TEST NUMBER: P246483

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.2	5.5
10°-20°	435.8	15.6
20°-30°	648.7	23.2
30°-40°	734.7	26.2
40°-50°	594.0	21.2
50°-60°	206.0	7.4
60°-70°	28.1	1.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1237.7	44.2
0°-40°	1972.4	70.4
0°-60°	2772.4	99.0
0°-90°	2801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1623	
5°	1615	153
15°	1546	436
25°	1412	649
35°	1180	735
45°	792	594
55°	210	206
65°	24	28
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246483

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	1622.6
2.5°	1620.6
5°	1614.7
7.5°	1602.7
10°	1587.8
12.5°	1568.0
15°	1546.1
17.5°	1518.3
20°	1487.5
22.5°	1451.7
25°	1412.0
27.5°	1364.3
30°	1309.6
32.5°	1248.0
35°	1180.4
37.5°	1105.9
40°	1022.5
42.5°	920.1
45°	791.9
47.5°	636.9
50°	476.0
52.5°	325.9
55°	209.7
57.5°	124.2
60°	72.5
62.5°	42.7
65°	23.8
67.5°	10.9
70°	3.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)