

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245763

Luminaire Tested: **LSR8B30D010 EC8B30840 8LBSOGPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30840 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3044.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245763

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245763

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53880
5°	53715
10°	53187
15°	52640
20°	52088
25°	51237
30°	49835
35°	47563
40°	44223
45°	37338
50°	25349
55°	13241
60°	5945
65°	2897
70°	1163
75°	715
80°	533
85°	354



TEST NUMBER: P245763

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.5	5.4
10°-20°	465.1	15.3
20°-30°	692.4	22.7
30°-40°	787.0	25.9
40°-50°	643.5	21.1
50°-60°	239.9	7.9
60°-70°	43.8	1.4
70°-80°	6.8	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1321.9	43.4
0°-40°	2108.9	69.3
0°-60°	2992.4	98.3
0°-90°	3044.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3044.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1747	
5°	1735	164
15°	1649	465
25°	1506	692
35°	1264	787
45°	856	644
55°	246	240
65°	40	44
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P245763

CATALOG NUMBER: LSR8B30D010 EC8B30840 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1747.3
2.5°	1744.3
5°	1735.3
7.5°	1719.4
10°	1698.6
12.5°	1674.7
15°	1648.9
17.5°	1619.1
20°	1587.3
22.5°	1549.6
25°	1505.9
27.5°	1456.2
30°	1399.6
32.5°	1335.0
35°	1263.5
37.5°	1187.0
40°	1098.6
42.5°	989.3
45°	856.2
47.5°	696.3
50°	528.4
52.5°	372.5
55°	246.3
57.5°	155.0
60°	96.4
62.5°	61.6
65°	39.7
67.5°	22.8
70°	12.9
72.5°	7.9
75°	6.0
77.5°	4.0
80°	3.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)