

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246253

Luminaire Tested: **LSR8B15D010 EC8B15830 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15830 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 955.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246253

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246253

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26929
5°	26252
10°	25554
15°	25076
20°	24424
25°	23558
30°	21617
35°	16575
40°	7886
45°	3005
50°	1463
55°	602
60°	148
65°	36
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246253

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	8.4
10°-20°	221.0	23.1
20°-30°	315.6	33.1
30°-40°	261.6	27.4
40°-50°	64.5	6.8
50°-60°	11.6	1.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	616.6	64.6
0°-40°	878.2	92.0
0°-60°	954.4	99.9
0°-90°	955.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	955.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	873	
5°	848	80
15°	786	221
25°	692	316
35°	440	262
45°	69	65
55°	11	12
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246253

CATALOG NUMBER: LSR8B15D010 EC8B15830 8LBW0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	873.3
2.5°	866.0
5°	848.1
7.5°	830.6
10°	816.1
12.5°	802.0
15°	785.5
17.5°	766.1
20°	744.3
22.5°	719.6
25°	692.4
27.5°	655.6
30°	607.1
32.5°	538.7
35°	440.3
37.5°	318.1
40°	195.9
42.5°	114.0
45°	68.9
47.5°	45.6
50°	30.5
52.5°	19.9
55°	11.2
57.5°	5.3
60°	2.4
62.5°	1.0
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)