

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246387

Luminaire Tested: **LSR8B30D010 EC8B30930 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201749)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30930 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 1887 (1 lamp)
Luminaire Lumens: 1468.6 lumens
Efficiency: 77.8%
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246387

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P246387

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	93	93	93	93	90	90	90	90	86	86	86		83	83	83		79	79	79	78
1	89	87	85	83	87	85	83	82	82	81	79		79	78	77		76	76	75	73
2	85	81	78	76	83	80	77	75	77	75	73		75	73	72		73	72	70	69
3	81	76	73	70	79	75	72	69	73	70	68		71	69	67		70	68	66	65
4	77	72	68	65	76	71	67	64	69	66	64		68	65	63		66	64	62	61
5	74	68	63	60	72	67	63	60	66	62	60		64	61	59		63	61	59	57
6	70	64	60	57	69	63	59	56	62	59	56		61	58	56		60	57	55	54
7	67	61	56	53	66	60	56	53	59	55	53		58	55	52		57	54	52	51
8	64	57	53	50	63	57	53	50	56	52	50		55	52	50		55	52	49	48
9	61	54	50	47	61	54	50	47	53	50	47		53	49	47		52	49	47	46
10	59	52	48	45	58	52	48	45	51	47	45		50	47	45		50	47	44	44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246387

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0B

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	210.3	14.3	11.1	0°	2344	
10°-20°	458.3	31.2	24.3	5°	2298	210
20°-30°	491.0	33.4	26.0	15°	1633	458
30°-40°	266.1	18.1	14.1	25°	1088	491
40°-50°	41.3	2.8	2.2	35°	417	266
50°-60°	1.2	0.1	0.1	45°	38	41
60°-70°	0.3	0.0	0.0	55°	0	1
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	1159.6	79.0	61.5	165°	0	0
0°-40°	1425.7	97.1	75.6	175°	0	0
0°-60°	1468.3	100.0	77.8	180°	0	0
0°-90°	1468.6	100.0	77.8			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	1468.6	100.0	77.8			



TEST NUMBER: P246387

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2344.0
2.5°	2342.4
5°	2298.2
7.5°	2188.5
10°	2018.2
12.5°	1819.9
15°	1633.4
17.5°	1475.6
20°	1338.0
22.5°	1214.4
25°	1088.5
27.5°	946.1
30°	779.0
32.5°	594.0
35°	416.8
37.5°	266.8
40°	153.9
42.5°	82.4
45°	38.0
47.5°	20.2
50°	7.0
52.5°	0.8
55°	0.0
57.5°	0.8
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246387

CATALOG NUMBER: LSR8B30D010 EC8B30930 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)