

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245329

Luminaire Tested: **LSR8B15D010 EC8B15840 8LBS0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245329  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15840 8LBS0WH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1631.0 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245329

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245329

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28487
5°	28595
10°	28957
15°	29523
20°	29944
25°	30067
30°	29144
35°	26603
40°	23013
45°	18115
50°	11686
55°	5736
60°	2356
65°	1036
70°	298
75°	107
80°	89
85°	0



TEST NUMBER: P245329

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.2	5.4
10°-20°	261.3	16.0
20°-30°	404.6	24.8
30°-40°	438.3	26.9
40°-50°	315.4	19.3
50°-60°	105.5	6.5
60°-70°	16.0	1.0
70°-80°	1.3	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.2	46.2
0°-40°	1192.5	73.1
0°-60°	1613.5	98.9
0°-90°	1631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1631.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	924	
5°	924	88
15°	925	261
25°	884	405
35°	707	438
45°	415	315
55°	107	106
65°	14	16
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245329

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	923.8
2.5°	923.8
5°	923.8
7.5°	924.3
10°	924.8
12.5°	925.7
15°	924.8
17.5°	921.0
20°	912.5
22.5°	899.7
25°	883.7
27.5°	858.2
30°	818.5
32.5°	766.6
35°	706.7
37.5°	642.0
40°	571.7
42.5°	496.1
45°	415.4
47.5°	328.1
50°	243.6
52.5°	167.1
55°	106.7
57.5°	63.7
60°	38.2
62.5°	23.1
65°	14.2
67.5°	7.1
70°	3.3
72.5°	1.4
75°	0.9
77.5°	0.9
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)