

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244897

Luminaire Tested: **LSR8B15D010 EC8B15840 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15840 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1631.0 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244897

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244897

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28517
5°	28428
10°	28171
15°	27892
20°	27594
25°	27158
30°	26413
35°	25207
40°	23363
45°	19724
50°	13533
55°	7462
60°	3750
65°	2109
70°	1154
75°	822
80°	515
85°	354



TEST NUMBER: P244897

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.1	5.3
10°-20°	246.4	15.1
20°-30°	366.9	22.5
30°-40°	416.7	25.6
40°-50°	340.7	20.9
50°-60°	133.5	8.2
60°-70°	31.1	1.9
70°-80°	7.5	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.3	42.9
0°-40°	1117.1	68.5
0°-60°	1591.2	97.6
0°-90°	1631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1631.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	925	
5°	918	87
15°	874	246
25°	798	367
35°	670	417
45°	452	341
55°	139	133
65°	29	31
75°	7	7
85°	1	1
90°	0	



TEST NUMBER: P244897

CATALOG NUMBER: LSR8B15D010 EC8B15840 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	924.8
2.5°	923.3
5°	918.4
7.5°	910.0
10°	899.7
12.5°	887.0
15°	873.7
17.5°	858.0
20°	840.9
22.5°	820.7
25°	798.2
27.5°	771.7
30°	741.8
32.5°	707.9
35°	669.6
37.5°	627.5
40°	580.4
42.5°	523.5
45°	452.3
47.5°	368.9
50°	282.1
52.5°	202.6
55°	138.8
57.5°	90.8
60°	60.8
62.5°	41.7
65°	28.9
67.5°	19.1
70°	12.8
72.5°	8.8
75°	6.9
77.5°	4.9
80°	2.9
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)