

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245283

Luminaire Tested: **LSR8B30D010 EC8B30935 8LBM0WH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245283  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30935 8LBM0WH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 3500 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2678.0 lumens  
Efficiency: N/A  
Efficacy: 98.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245283

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P245283

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	103666
5°	105656
10°	100737
15°	88950
20°	77083
25°	65132
30°	48945
35°	32773
40°	18352
45°	7374
50°	2552
55°	710
60°	401
65°	350
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245283

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	319.4	11.9
10°-20°	777.2	29.0
20°-30°	862.4	32.2
30°-40°	546.3	20.4
40°-50°	151.6	5.7
50°-60°	17.4	0.6
60°-70°	3.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1958.9	73.1
0°-40°	2505.3	93.5
0°-60°	2674.2	99.9
0°-90°	2678.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2678.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3362	
5°	3413	319
15°	2786	777
25°	1914	862
35°	871	546
45°	169	152
55°	13	17
65°	5	3
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245283

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3361.8
2.5°	3386.7
5°	3413.3
7.5°	3360.1
10°	3217.2
12.5°	3013.3
15°	2786.3
17.5°	2563.3
20°	2349.0
22.5°	2138.6
25°	1914.3
27.5°	1651.9
30°	1374.6
32.5°	1106.0
35°	870.6
37.5°	657.9
40°	455.9
42.5°	283.5
45°	169.1
47.5°	97.2
50°	53.2
52.5°	26.1
55°	13.2
57.5°	9.9
60°	6.5
62.5°	3.4
65°	4.8
67.5°	2.4
70°	0.0
72.5°	0.7
75°	0.0
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245283

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBM0WH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)