

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244491

Luminaire Tested: **LSR8B30D010 EC8B30935 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B30D010 EC8B30935 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2892.0 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 27.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244491

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244491

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51753
5°	51582
10°	51189
15°	50830
20°	50483
25°	49822
30°	48279
35°	45553
40°	41401
45°	34067
50°	22706
55°	11828
60°	5575
65°	2926
70°	1461
75°	1013
80°	764
85°	601



TEST NUMBER: P244491

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.1	5.5
10°-20°	449.4	15.5
20°-30°	672.2	23.2
30°-40°	751.9	26.0
40°-50°	589.9	20.4
50°-60°	215.2	7.4
60°-70°	43.9	1.5
70°-80°	9.4	0.3
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1279.7	44.2
0°-40°	2031.6	70.2
0°-60°	2836.7	98.1
0°-90°	2892.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2892.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1678	
5°	1666	158
15°	1592	449
25°	1464	672
35°	1210	752
45°	781	590
55°	220	215
65°	40	44
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P244491

CATALOG NUMBER: LSR8B30D010 EC8B30935 8LBS0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1678.3
2.5°	1675.7
5°	1666.4
7.5°	1652.7
10°	1634.8
12.5°	1614.3
15°	1592.2
17.5°	1567.4
20°	1538.4
22.5°	1504.3
25°	1464.3
27.5°	1414.8
30°	1355.9
32.5°	1286.9
35°	1210.1
37.5°	1124.0
40°	1028.5
42.5°	915.1
45°	781.2
47.5°	630.2
50°	473.3
52.5°	331.7
55°	220.0
57.5°	140.7
60°	90.4
62.5°	59.7
65°	40.1
67.5°	25.6
70°	16.2
72.5°	11.1
75°	8.5
77.5°	6.0
80°	4.3
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)