

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246519

Luminaire Tested: **LSR8B30D010 EC8B30950 8LBS0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B30950 8LBS0B  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2600.0 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246519

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0B

### Luminous Intensity Polar Plot





TEST NUMBER: P246519

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46446
5°	46394
10°	46151
15°	45817
20°	45308
25°	44592
30°	43284
35°	41247
40°	38205
45°	32057
50°	21194
55°	10462
60°	4151
65°	1613
70°	252
75°	0
80°	0
85°	0



TEST NUMBER: P246519

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.2	5.5
10°-20°	404.5	15.6
20°-30°	602.1	23.2
30°-40°	682.0	26.2
40°-50°	551.4	21.2
50°-60°	191.2	7.4
60°-70°	26.1	1.0
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1148.9	44.2
0°-40°	1830.9	70.4
0°-60°	2573.5	99.0
0°-90°	2600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2600.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1506	
5°	1499	142
15°	1435	405
25°	1311	602
35°	1096	682
45°	735	551
55°	195	191
65°	22	26
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246519

CATALOG NUMBER: LSR8B30D010 EC8B30950 8LBS0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1506.2
2.5°	1504.3
5°	1498.8
7.5°	1487.7
10°	1473.9
12.5°	1455.4
15°	1435.2
17.5°	1409.3
20°	1380.7
22.5°	1347.5
25°	1310.6
27.5°	1266.4
30°	1215.6
32.5°	1158.5
35°	1095.7
37.5°	1026.6
40°	949.1
42.5°	854.1
45°	735.1
47.5°	591.2
50°	441.8
52.5°	302.5
55°	194.6
57.5°	115.3
60°	67.3
62.5°	39.7
65°	22.1
67.5°	10.1
70°	2.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)