

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245695

Luminaire Tested: **LSR8B15D010 EC8B15850 8LBM0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15850 8LBM0GPH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1365.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245695

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBM0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245695

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBM0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53393
5°	52037
10°	46658
15°	41546
20°	37908
25°	34426
30°	28233
35°	18592
40°	9262
45°	3445
50°	1051
55°	118
60°	74
65°	0
70°	45
75°	203
80°	0
85°	177



TEST NUMBER: P245695

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBM0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.1	11.3
10°-20°	366.5	26.8
20°-30°	456.5	33.4
30°-40°	308.0	22.6
40°-50°	72.8	5.3
50°-60°	5.3	0.4
60°-70°	0.9	0.1
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	977.1	71.6
0°-40°	1285.2	94.2
0°-60°	1363.3	99.9
0°-90°	1365.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1365.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1732	
5°	1681	154
15°	1301	366
25°	1012	456
35°	494	308
45°	79	73
55°	2	5
65°	0	1
75°	2	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245695

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBM0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1731.5
2.5°	1728.7
5°	1681.1
7.5°	1595.4
10°	1490.1
12.5°	1389.9
15°	1301.4
17.5°	1225.2
20°	1155.2
22.5°	1087.5
25°	1011.8
27.5°	913.3
30°	792.9
32.5°	647.3
35°	493.9
37.5°	353.4
40°	230.1
42.5°	137.7
45°	79.0
47.5°	44.3
50°	21.9
52.5°	10.1
55°	2.2
57.5°	0.5
60°	1.2
62.5°	1.7
65°	0.0
67.5°	1.2
70°	0.5
72.5°	0.5
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.5
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245695

CATALOG NUMBER: LSR8B15D010 EC8B15850 8LBM0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)