

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245785

Luminaire Tested: **LSR8B15D010 EC8B15935 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B15D010 EC8B15935 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1301.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245785

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245785

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23029
5°	22959
10°	22733
15°	22497
20°	22262
25°	21898
30°	21300
35°	20328
40°	18899
45°	15961
50°	10837
55°	5661
60°	2541
65°	1240
70°	496
75°	298
80°	231
85°	142



TEST NUMBER: P245785

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.3	5.4
10°-20°	198.8	15.3
20°-30°	295.9	22.7
30°-40°	336.4	25.9
40°-50°	275.1	21.1
50°-60°	102.5	7.9
60°-70°	18.8	1.4
70°-80°	2.9	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.0	43.4
0°-40°	901.4	69.3
0°-60°	1278.9	98.3
0°-90°	1301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	747	
5°	742	70
15°	705	199
25°	644	296
35°	540	336
45°	366	275
55°	105	103
65°	17	19
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245785

CATALOG NUMBER: LSR8B15D010 EC8B15935 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	746.8
2.5°	745.5
5°	741.7
7.5°	734.9
10°	726.0
12.5°	715.8
15°	704.7
17.5°	692.0
20°	678.4
22.5°	662.3
25°	643.6
27.5°	622.4
30°	598.2
32.5°	570.6
35°	540.0
37.5°	507.3
40°	469.5
42.5°	422.8
45°	366.0
47.5°	297.6
50°	225.9
52.5°	159.2
55°	105.3
57.5°	66.2
60°	41.2
62.5°	26.3
65°	17.0
67.5°	9.8
70°	5.5
72.5°	3.4
75°	2.5
77.5°	1.7
80°	1.3
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)