

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246603

Luminaire Tested: **LSR8B30D010 EC8B309730 8LBW0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246603  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B30D010 EC8B309730 8LBW0MW  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
97 CRI 3000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2323.0 lumens  
Efficiency: N/A  
Efficacy: 85.7 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 27.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246603

CATALOG NUMBER: LSR8B30D010 EC8B309730 8LBW0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246603

CATALOG NUMBER: LSR8B30D010 EC8B309730 8LBW0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246603

CATALOG NUMBER: LSR8B30D010 EC8B309730 8LBW0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.8	6.1
10°-20°	390.6	16.8
20°-30°	572.8	24.7
30°-40°	523.6	22.5
40°-50°	259.2	11.2
50°-60°	191.7	8.3
60°-70°	147.4	6.3
70°-80°	76.8	3.3
80°-90°	19.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.2	47.6
0°-40°	1628.8	70.1
0°-60°	2079.7	89.5
0°-90°	2323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2323.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1539	
5°	1508	142
15°	1383	391
25°	1254	573
35°	869	524
45°	315	259
55°	212	192
65°	150	147
75°	72	77
85°	16	19
90°	0	



TEST NUMBER: P246603

CATALOG NUMBER: LSR8B30D010 EC8B309730 8LBW0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1539.2
2.5°	1531.0
5°	1507.5
7.5°	1475.8
10°	1443.4
12.5°	1411.7
15°	1383.0
17.5°	1355.7
20°	1326.2
22.5°	1293.1
25°	1254.0
27.5°	1200.2
30°	1125.1
32.5°	1019.7
35°	868.7
37.5°	681.5
40°	503.2
42.5°	380.9
45°	314.6
47.5°	278.5
50°	252.0
52.5°	230.6
55°	212.2
57.5°	196.7
60°	183.5
62.5°	169.5
65°	150.3
67.5°	129.7
70°	109.0
72.5°	89.9
75°	71.5
77.5°	55.3
80°	40.5
82.5°	28.0
85°	16.2
87.5°	5.9
90°	0.0

(END OF REPORT)