

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245725

Luminaire Tested: **LSR8B15D010 EC8B15950 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B15D010 EC8B15950 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
90 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1243.1 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245725

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245725

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	48620
5°	47385
10°	42490
15°	37833
20°	34522
25°	31350
30°	25712
35°	16929
40°	8437
45°	3135
50°	955
55°	108
60°	68
65°	0
70°	45
75°	191
80°	0
85°	177



TEST NUMBER: P245725

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.4	11.3
10°-20°	333.7	26.8
20°-30°	415.7	33.4
30°-40°	280.5	22.6
40°-50°	66.3	5.3
50°-60°	4.8	0.4
60°-70°	0.9	0.1
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	889.8	71.6
0°-40°	1170.3	94.1
0°-60°	1241.4	99.9
0°-90°	1243.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1243.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1577	
5°	1531	140
15°	1185	334
25°	921	416
35°	450	281
45°	72	66
55°	2	5
65°	0	1
75°	2	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245725

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1576.7
2.5°	1574.2
5°	1530.8
7.5°	1452.8
10°	1357.0
12.5°	1265.7
15°	1185.1
17.5°	1115.7
20°	1052.0
22.5°	990.3
25°	921.4
27.5°	831.7
30°	722.1
32.5°	589.5
35°	449.7
37.5°	321.8
40°	209.6
42.5°	125.4
45°	71.9
47.5°	40.3
50°	19.9
52.5°	9.2
55°	2.0
57.5°	0.5
60°	1.1
62.5°	1.6
65°	0.0
67.5°	1.1
70°	0.5
72.5°	0.5
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.5
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245725

CATALOG NUMBER: LSR8B15D010 EC8B15950 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)