

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246256

Luminaire Tested: **LSR8B40D010 EC8B40830 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B40830 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2693.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246256

CATALOG NUMBER: LSR8B40D010 EC8B40830 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246256

CATALOG NUMBER: LSR8B40D010 EC8B40830 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | | 101 | 99 | 98 | | 97 | 96 | 95 | 93 |
| 2 | 107 | 102 | 98 | 95 | 105 | 101 | 97 | 94 | 97 | 94 | 92 | | 94 | 92 | 90 | | 92 | 90 | 88 | 86 |
| 3 | 102 | 95 | 90 | 86 | 100 | 94 | 89 | 85 | 91 | 87 | 84 | | 89 | 85 | 82 | | 86 | 84 | 81 | 80 |
| 4 | 96 | 88 | 83 | 78 | 94 | 87 | 82 | 78 | 85 | 80 | 77 | | 83 | 79 | 76 | | 81 | 78 | 75 | 74 |
| 5 | 91 | 82 | 76 | 72 | 89 | 81 | 76 | 71 | 80 | 75 | 71 | | 78 | 74 | 70 | | 76 | 73 | 70 | 68 |
| 6 | 86 | 77 | 71 | 66 | 85 | 76 | 70 | 66 | 74 | 69 | 65 | | 73 | 68 | 65 | | 72 | 68 | 65 | 63 |
| 7 | 82 | 72 | 66 | 61 | 80 | 71 | 65 | 61 | 70 | 64 | 61 | | 69 | 64 | 60 | | 67 | 63 | 60 | 58 |
| 8 | 77 | 67 | 61 | 57 | 76 | 67 | 61 | 57 | 66 | 60 | 56 | | 65 | 60 | 56 | | 64 | 59 | 56 | 54 |
| 9 | 73 | 63 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 56 | 52 | | 61 | 56 | 52 | | 60 | 55 | 52 | 51 |
| 10 | 70 | 59 | 53 | 49 | 68 | 59 | 53 | 49 | 58 | 53 | 49 | | 57 | 52 | 49 | | 57 | 52 | 49 | 47 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 75938 |
| 5° | 74027 |
| 10° | 72058 |
| 15° | 70715 |
| 20° | 68876 |
| 25° | 66435 |
| 30° | 60955 |
| 35° | 46739 |
| 40° | 22236 |
| 45° | 8469 |
| 50° | 4130 |
| 55° | 1688 |
| 60° | 419 |
| 65° | 102 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P246256

CATALOG NUMBER: LSR8B40D010 EC8B40830 8LBW0B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 225.5 | 8.4 |
| 10°-20° | 623.3 | 23.1 |
| 20°-30° | 890.1 | 33.1 |
| 30°-40° | 737.7 | 27.4 |
| 40°-50° | 181.9 | 6.8 |
| 50°-60° | 32.7 | 1.2 |
| 60°-70° | 1.8 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1738.9 | 64.6 |
| 0°-40° | 2476.5 | 92.0 |
| 0°-60° | 2691.1 | 99.9 |
| 0°-90° | 2693.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2693.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2463 | |
| 5° | 2392 | 225 |
| 15° | 2215 | 623 |
| 25° | 1953 | 890 |
| 35° | 1242 | 738 |
| 45° | 194 | 182 |
| 55° | 31 | 33 |
| 65° | 1 | 2 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P246256

CATALOG NUMBER: LSR8B40D010 EC8B40830 8LBW0B

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2462.6 |
| 2.5° | 2442.1 |
| 5° | 2391.5 |
| 7.5° | 2342.3 |
| 10° | 2301.3 |
| 12.5° | 2261.6 |
| 15° | 2215.1 |
| 17.5° | 2160.4 |
| 20° | 2098.9 |
| 22.5° | 2029.2 |
| 25° | 1952.6 |
| 27.5° | 1848.7 |
| 30° | 1711.9 |
| 32.5° | 1519.1 |
| 35° | 1241.6 |
| 37.5° | 897.0 |
| 40° | 552.4 |
| 42.5° | 321.3 |
| 45° | 194.2 |
| 47.5° | 128.5 |
| 50° | 86.1 |
| 52.5° | 56.1 |
| 55° | 31.4 |
| 57.5° | 15.0 |
| 60° | 6.8 |
| 62.5° | 2.7 |
| 65° | 1.4 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)