

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245260

Luminaire Tested: **LSR8B40D010 EC8B40840 8LBM0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B40D010 EC8B40840 8LBM0WH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4438.0 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245260

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBM0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245260

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBM0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	73		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65		72	68	64		71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57		65	60	57		64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171795
5°	175095
10°	166940
15°	147406
20°	127740
25°	107938
30°	81116
35°	54313
40°	30416
45°	12219
50°	4231
55°	1172
60°	666
65°	576
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P245260

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBM0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	529.2	11.9
10°-20°	1287.9	29.0
20°-30°	1429.2	32.2
30°-40°	905.5	20.4
40°-50°	251.2	5.7
50°-60°	28.8	0.6
60°-70°	5.7	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3246.3	73.1
0°-40°	4151.8	93.6
0°-60°	4431.8	99.9
0°-90°	4438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5571	
5°	5657	529
15°	4617	1288
25°	3172	1429
35°	1443	905
45°	280	251
55°	22	29
65°	8	6
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245260

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBM0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	5571.2
2.5°	5612.4
5°	5656.6
7.5°	5568.4
10°	5331.5
12.5°	4993.7
15°	4617.4
17.5°	4247.9
20°	3892.7
22.5°	3544.2
25°	3172.4
27.5°	2737.6
30°	2278.1
32.5°	1833.0
35°	1442.8
37.5°	1090.3
40°	755.6
42.5°	469.9
45°	280.2
47.5°	161.1
50°	88.2
52.5°	43.2
55°	21.8
57.5°	16.4
60°	10.8
62.5°	5.7
65°	7.9
67.5°	4.0
70°	0.0
72.5°	1.1
75°	0.0
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245260

CATALOG NUMBER: LSR8B40D010 EC8B40840 8LBM0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)