

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250460

Luminaire Tested: **LSR8B150D010 EC8B150827 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250460  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LSR8B150D010 EC8B150827 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT- CYLINDEC  
80 CRI 2700 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 13202.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 158.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250460

CATALOG NUMBER: LSR8B150D010 EC8B150827 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250460

CATALOG NUMBER: LSR8B150D010 EC8B150827 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	516311
5°	503258
10°	451144
15°	401806
20°	366547
25°	333031
30°	273082
35°	179721
40°	89654
45°	33370
50°	10137
55°	1226
60°	709
65°	0
70°	514
75°	2049
80°	0
85°	2017



TEST NUMBER: P250460

CATALOG NUMBER: LSR8B150D010 EC8B150827 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1490.6	11.3
10°-20°	3544.2	26.8
20°-30°	4415.5	33.4
30°-40°	2978.4	22.6
40°-50°	704.3	5.3
50°-60°	51.5	0.4
60°-70°	9.2	0.1
70°-80°	6.8	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9450.4	71.6
0°-40°	12428.7	94.1
0°-60°	13184.5	99.9
0°-90°	13202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13202.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16744	
5°	16258	###
15°	12586	3544
25°	9788	4416
35°	4774	2978
45°	765	704
55°	23	51
65°	0	9
75°	17	7
85°	6	2
90°	0	



TEST NUMBER: P250460

CATALOG NUMBER: LSR8B150D010 EC8B150827 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16743.6
2.5°	16715.1
5°	16258.2
7.5°	15430.1
10°	14408.0
12.5°	13442.9
15°	12586.3
17.5°	11849.5
20°	11170.0
22.5°	10519.0
25°	9788.1
27.5°	8834.4
30°	7669.4
32.5°	6258.9
35°	4774.2
37.5°	3415.0
40°	2227.2
42.5°	1330.6
45°	765.2
47.5°	428.3
50°	211.3
52.5°	97.1
55°	22.8
57.5°	5.7
60°	11.5
62.5°	17.2
65°	0.0
67.5°	11.5
70°	5.7
72.5°	5.7
75°	17.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	5.7
87.5°	0.0
90°	0.0

(END OF REPORT)