

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249795

Luminaire Tested: **LSR8B150D010 EC8B150830 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B150830 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13705.0 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249795

CATALOG NUMBER: LSR8B150D010 EC8B150830 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249795

CATALOG NUMBER: LSR8B150D010 EC8B150830 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	579639
5°	572521
10°	528750
15°	461057
20°	394942
25°	330588
30°	251508
35°	155907
40°	76917
45°	36610
50°	17798
55°	8725
60°	5433
65°	3721
70°	2092
75°	1656
80°	1651
85°	1628



TEST NUMBER: P249795

CATALOG NUMBER: LSR8B150D010 EC8B150830 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1714.1	12.5
10°-20°	4024.2	29.4
20°-30°	4398.3	32.1
30°-40°	2617.3	19.1
40°-50°	717.9	5.2
50°-60°	162.6	1.2
60°-70°	50.2	0.4
70°-80°	15.3	0.1
80°-90°	5.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10136.5	74.0
0°-40°	12753.9	93.1
0°-60°	13634.4	99.5
0°-90°	13705.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13705.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18797	
5°	18496	###
15°	14442	4024
25°	9716	4398
35°	4142	2617
45°	840	718
55°	162	163
65°	51	50
75°	14	15
85°	5	5
90°	0	



TEST NUMBER: P249795

CATALOG NUMBER: LSR8B150D010 EC8B150830 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	18797.3
1°	18834.4
2°	18811.2
3°	18764.8
4°	18658.2
5°	18495.8
6°	18287.1
7°	18008.9
8°	17684.2
9°	17308.5
10°	16886.5
11°	16436.6
12°	15954.3
13°	15458.0
14°	14943.2
15°	14442.3
16°	13950.7
17°	13468.4
18°	12986.0
19°	12503.7
20°	12035.3
22.5°	10857.3
25°	9716.3
27.5°	8459.5
30°	7063.5
32.5°	5565.4
35°	4141.6
37.5°	2880.1
40°	1910.8
42.5°	1252.2
45°	839.5
47.5°	556.5
50°	371.0
52.5°	227.3
55°	162.3
57.5°	115.9
60°	88.1
62.5°	64.9
65°	51.0
67.5°	32.5
70°	23.2
72.5°	18.6
75°	13.9
77.5°	9.3
80°	9.3



TEST NUMBER: P249795

CATALOG NUMBER: LSR8B150D010 EC8B150830 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	4.6
85°	4.6
87.5°	4.6
90°	0.0

(END OF REPORT)