

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243809

Luminaire Tested: **LSR8B50D010 EC8B50830 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B50D010 EC8B50830 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5586.0 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243809

CATALOG NUMBER: LSR8B50D010 EC8B50830 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243809

CATALOG NUMBER: LSR8B50D010 EC8B50830 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99108
5°	102040
10°	110544
15°	120951
20°	125830
25°	125369
30°	117598
35°	98609
40°	68657
45°	39322
50°	21113
55°	8709
60°	2171
65°	555
70°	279
75°	179
80°	266
85°	0



TEST NUMBER: P243809

CATALOG NUMBER: LSR8B50D010 EC8B50830 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.3	5.8
10°-20°	1067.8	19.1
20°-30°	1680.1	30.1
30°-40°	1598.2	28.6
40°-50°	736.8	13.2
50°-60°	167.4	3.0
60°-70°	11.0	0.2
70°-80°	2.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3070.2	55.0
0°-40°	4668.4	83.6
0°-60°	5572.6	99.8
0°-90°	5586.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5586.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3214	
5°	3296	322
15°	3789	1068
25°	3685	1680
35°	2620	1598
45°	902	737
55°	162	167
65°	8	11
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P243809

CATALOG NUMBER: LSR8B50D010 EC8B50830 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3214.0
1°	3212.5
2°	3218.6
3°	3236.9
4°	3264.4
5°	3296.5
6°	3336.3
7°	3379.1
8°	3423.4
9°	3475.3
10°	3530.4
11°	3585.4
12°	3643.5
13°	3698.5
14°	3748.9
15°	3788.7
16°	3817.7
17°	3837.6
18°	3846.7
19°	3845.2
20°	3834.5
21°	3816.2
22°	3793.2
23°	3762.7
24°	3727.5
25°	3684.7
26°	3634.3
27°	3570.1
28°	3493.7
29°	3405.0
30°	3302.7
32.5°	2995.5
35°	2619.5
37.5°	2182.4
40°	1705.6
42.5°	1260.8
45°	901.7
47.5°	638.8
50°	440.1
52.5°	281.2
55°	162.0
57.5°	81.0
60°	35.2
62.5°	13.8
65°	7.6



TEST NUMBER: P243809

CATALOG NUMBER: LSR8B50D010 EC8B50830 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	4.6
70°	3.1
72.5°	3.1
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)