

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250446

Luminaire Tested: **LSR8B150D010 EC8B1509727 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LSR8B150D010 EC8B1509727 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT- CYLINDEC
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6436.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250446

CATALOG NUMBER: LSR8B150D010 EC8B1509727 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250446

CATALOG NUMBER: LSR8B150D010 EC8B1509727 8LBN0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250446

CATALOG NUMBER: LSR8B150D010 EC8B1509727 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	923.2	14.3
10°-20°	2006.5	31.2
20°-30°	2154.2	33.5
30°-40°	1164.3	18.1
40°-50°	181.6	2.8
50°-60°	5.0	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5083.9	79.0
0°-40°	6248.2	97.1
0°-60°	6434.8	100.0
0°-90°	6436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6436.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10284	
5°	10081	923
15°	7164	2007
25°	4775	2154
35°	1829	1164
45°	168	182
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250446

CATALOG NUMBER: LSR8B150D010 EC8B1509727 8LBN0B

CANDELA DISTRIBUTION (FULL):

0°	
0°	10284.1
1°	10303.6
2°	10293.9
3°	10258.7
4°	10191.0
5°	10081.3
6°	9930.2
7°	9727.1
8°	9472.8
9°	9180.1
10°	8854.6
11°	8513.2
12°	8159.0
13°	7805.2
14°	7476.4
15°	7164.2
16°	6877.6
17°	6600.7
18°	6343.1
19°	6101.9
20°	5869.8
21°	5644.4
22°	5431.7
23°	5219.5
24°	4997.3
25°	4775.0
26°	4549.5
27°	4292.1
28°	4008.6
29°	3719.2
30°	3416.3
31°	3091.2
32°	2765.7
33°	2443.8
34°	2118.7
35°	1828.8
37.5°	1168.8
40°	676.2
42.5°	360.7
45°	167.6
47.5°	90.3
50°	29.2
52.5°	3.3
55°	0.0
57.5°	3.3



TEST NUMBER: P250446

CATALOG NUMBER: LSR8B150D010 EC8B1509727 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	3.3
62.5°	0.0
65°	0.0
67.5°	3.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)